Provided by www.AAATesters.com

Handheld Power Meters FOT-10A and FOT-20A



Versatility in the Field

The FOT-10A and FOT-20A Power Meters are compact, accurate, rugged and easy-to-use instruments for both power and loss testing. Like all of EXFO's handheld power meters, the FOT-10A and FOT-20A can be calibrated to a custom wavelength, free of charge.

Key Features

- Direct loss measurement in dB
- Five electronically calibrated wavelengths
- Shockproof holster also acts as storage compartment for fiberoptic adapters and replacement battery
- Auto-off function
- FOT-10A: power measurements in dBm
- FOT-20A: power measurements in dB, dBm and W

Performance

The FOT-10A and FOT-20A incorporate EXFO's linear amplification technology and are traceable to NIST. They offer five calibrated wavelengths, and perform 2 kHz signal detection for fiber identification. Unit configurations are available with germanium or high-power germanium detectors. An electrical offset nulling feature makes the FOT-10A and FOT-20A ideal for operation in extreme temperature conditions.

FOT-10A

FOT-20A

Ruggedness

The FOT-10A and FOT-20A Power Meters meet Telcordia's strict drop-test requirements. A holster is included for added durability and portability of connector and battery accessories. A complete range of EXFO fiber-optic adapters is available for connector interface. A single 9 V battery powers these units for over 14 hours.

Custom Calibration

Like all EXFO power meters, the FOT-10A and FOT-20A can be calibrated at a custom wavelength.

Applications

- Transmitter power measurements (dBm and W)
- Fiber-link loss testing (dB)
- Component insertion-loss testing (dB)
- Fiber identification with 2 kHz signals
- LAN installation and maintenance applications

- Accessories
- Battery
- AC adapter/charger
- Rigid carrying case
- Shockproof holster

Specifications

| Models | FOT-12A | FOT-12AX | FOT-22A | FOT-22AX |
|--|---|---|-----------------|-----------------|
| Detector type | Ge (2 mm) | GeX (2 mm) | Ge (2 mm) | GeX (2 mm) |
| Standard calibrated | 780, 850, 1300, | 780, 850, 1300, | 780, 850, 1300, | 780, 850, 1300, |
| wavelengths (nm) | 1310, 1550 | 1310, 1550 | 1310, 1550 | 1310, 1550 |
| Measurement range ¹ (dBm) | 6 to -60 | 21 to -50 | 6 to -60 | 21 to -50 |
| Resolution ³ (dB) | 0.05 | 0.05 | 0.05 | 0.05 |
| Uncertainty ^{2,3} (%) | + 5 | + 5 | ± 5 | + 5 |
| oncertainty (10) | 10 | <u> </u> | | |
| General Specificatio | ns | | | |
| General Specificatio Size (H × W × D) | | (8 ³ / ₄ in × 4 ¹ / ₁₆ in × 2 ¹ / ₄ in) | | |
| General Specificatio Size (H × W × D) | ns | | | |
| General Specificatio Size (H × W × D) Weight | ns 22.2 cm × 10.3 cm × 5.9 cm | – (8 3/4 in × 4 1/16 in × 2 1/4 in) | | |
| General Specificatio Size (H × W × D) Weight unit | ns 22.2 cm × 10.3 cm × 5.9 cm 0.56 kg | - (8 ³ / ₄ in × 4 ¹ / ₁₆ in × 2 ¹ / ₄ in) (1.25 lb) | | |

Standard Accessories

User Guide, carrying case, 9 V alkaline battery, AC adapter, connector adapter, protective holster, shoulder strap and Certificate of Calibration.

Notes

1. Measured at 1300 nm.

2. Traceable to NIST.

 Resolution and uncertainty are functions of detected power levels. Values supplied are for a -35 dBm power level.

Ordering Information

| Power Meter FOT-1XA-XX | |
|---|--|
| Model FOT-12A = Ge FOT-12AX = High-Power Ge | Model FOT-22A = Ge FOT-22AX = High-Power Ge |
| Example: FOT-12AX-FOA-22 | Example: FOT-22AX-FOA-22 |
| | Specify the model number and the connector adapter you wish to obtain (one free connector adapter included): FOA-12 = Biconic FOA-14 = D4: D4,D4/PC FOA-16 = SMA/905, SMA/906 FOA-22 = FC: FC (PC/SPC/UPC/APC), NEC-D3 FOA-24 = Radiall VFO/DF (straight/slant) FOA-28 = DIN 47256 (LSA): DIN 47256 (PC/APC) FOA-32 = ST: ST (PC/SPC/UPC) FOA-32 = ST: ST (PC/SPC/UPC) FOA-34 = Mini-BNC FOA-40 = Diamond HMS-0HFS-3 (3.5 mm) FOA-42 = Radiall PFO FOA-44 = Radiall MFO FOA-48 = HP HFBR-4501-HFBR-4503 FOA-52 = Biconic Bayonet FOA-54 = SC: SC (PC/SPC/UPC/APC) FOA-68 = AT&T Rotary Splice FOA-76 = FSMA HMS-10/AG, HFS-10/AG FOA-78 = Radiall EC FOA-78 = Radiall EC FOA-78 = Diamond HMS-10, HFS-13 FOA-96 = E-2000 |
| | FOA-97 = LX.5 FOA-98 = LC FOA-99 = MU |

| Find out more about EXFO's extensive line of high-performance portable instruments by visiting our Web site at www.exfo.com | | | | | | |
|---|--|------------------------------------|--|--|--|--|
| Rugged Handheld Solutions UNIVERSAL TEST SYSTEM Optical Fiber DWDM Test Systems Protocol | | | | | | |
| • OLTS • Power Meter • Light Source • Talk Set | | OTDR OLTS ORL Switch ORL | | | | |
| CORPORATE HEADQUARTERS | 400 Godin Avenue | Vanier (Quebec) G1M 2K2 CANADA | Tel.: 1 418 683-0211 · Fax: 1 418 683-2170 | | | |
| EXFO AMERICA | 4275 Kellway Circle, Suite 122 | Addison TX 75001 USA | Tel.: 1 800 663-3936 · Fax: 1 972 836-0164 | | | |
| EXFO EUROPE | Le Dynasteur, 10/12 rue Andras Beck | 92366 Meudon la Forêt Cedex FRANCE | Tel.: +33.1.40.83.85.85 · Fax: +33.1.40.83.04.42 | | | |
| EXFO ASIA-PACIFIC | 151 Chin Swee Road, #03-29 Manhattan House | SINGAPORE 169876 | Tel.: +65 6333 8241 · Fax: +65 6333 8242 | | | |
| EXFO CHINA | Beijing New Century Hotel Office Tower, Room 1754-1755 | Beijing 100044 P. R. China | Tel.: +86 (10) 6849 2738 · Fax: +86 (10) 6849 2662 | | | |
| | No. 6 Southern Capital Gym Road | | | | | |
| TOLL-FREE (USA and Canada) | Tel.: 1 800 663-3936 | www.exfo.com • info@exfo.com | | | | |

EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no

EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. **Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.** For the most recent version of this spec sheet, please go to the EXFO website at **http://www.exfo.com/support/techdocs.asp** In case of discrepancy, the Web version takes precedence over any printed literature. All names, trademarks, products and services mentioned are registered or unregistered trademarks of their respective owners.

EXFO

EVEN's

