EXFO BFA-3000 Specs Provided by www.AAATesters.com

BFA FIBRE ADAPTERS

BFA Series



The BFA-3000 Universal Bare Fiber Adapter

The BFA-3000 is an essential accessory for performing fast, accurate and repeatable power measurements on non-connectorized fiber or components. Its innovative, spring-loaded mechanism enables easy, consistent positioning of bare fibers for connection to a power meter via the FOA-3000 Adapter. This bare fiber adapter is perfect for repeatable power measurements using EXFO's OHS-1713-UH Ultra-High-Power[™] Optical Head.


Whether in an R&D setup or a manufacturing environment, the BFA-3000 complements EXFO's IQS-1500, PM-1600, IQS-1600, IQS-1700 and OHS-1700 power meters (detectors \geq 3 mm), as well as the detectors used in the IQS-12001B Cable Assembly Test System.

BFA-200 Series Bare Fiber Adapters


These adapaters easily and quickly connect bare fibers, thanks to their push-button locking system. Designed for both field applications and component testing, they ensure reliable connections and are the ideal complement to EXFO's complete range of fiber-optic test instruments. BFA-200 series adapters are available for FC, SC, ST and E-2000 connectors.

- Designed for singlemode or multimode fiber, both coated or non-coated, bare fiber or non connectorized components
- Easy fiber positioning
- Repeatable measurements, from test to test, from user to user





BFA-3000 in open position. Fiber is in place. Yellow portion of fiber is unstripped.



BFA-3000, FOA-3000 and receptacle assembly.

ORDERING INFORMATION





EXEO Corporate Headquarters > 400 Godin A	Avenue Quebec City (Quebec)	G1M 2K2 CANADA	Tel: 1 418 683-0211 Fa	x: 1 418 683-2170 info@EXEO.c	om ^r

		Toll-free: 1 800 663-3936 (USA and Canada) www.EXFO.co			
EXFO America	3701 Plano Parkway, Suite 160	Plano, TX 75075 USA	Tel.: 1 800 663-3936	Fax: 1 972 836-0164	
EXFO Europe	Omega Enterprise Park, Electron Way	Chandlers Ford, Hampshire S053 4SE ENGLAND	Tel.: +44 2380 246810	Fax: +44 2380 246801	
EXFO Asia	151 Chin Swee Road, #03-29 Manhattan House	SINGAPORE 169876	Tel.: +65 6333 8241	Fax: +65 6333 8242	
	No.88 Fuhua, First Road	Shenzhen 518048, CHINA	Tel.: +86 (755) 8203 2300	Fax: +86 (755) 8203 2306	
	Central Tower, Room 801, Futian District				
	Beijing New Century Hotel Office Tower, Room 1754-1755	Beijing 100044 P. R. CHINA	Tel.: +86 (10) 6849 2738	Fax: +86 (10) 6849 2662	
	No. 6 Southern Capital Gym Road				

Ins device complies with Part 15 of the HCL Kules. Uperation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. EVFO has made every effort to ensure that the information contained in this specification sheet is accurate. All of EVFOS manufactured products are compliant with the European Union's WEEE directive. For more information, please wist www.EXFO.com/recycle. However, we accept no responsibility for any errors or missions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to \$I standards and practices. Contact EXFO of prices and availability or to obtain the phone number of your local EXFO distributor.

For the most recent version of this spec sheet, please go to the EXFO website at http://www.EXFO.com/specs

In case of discrepancy, the Web version takes precedence over any printed literature.

