



Bluetooth®

70R+

### Fujikura 70R+ Fusion Splicer

The Fujikura 70R+ ribbon splicer utilizes precision, fixed v-groove technology for splicing ribbon fiber up to 12 fibers, including single fibers. Incorporating the proven ruggedized features pioneered by Fujikura, the 70R+ has automated and enhanced user control features to increase splicing efficiency. A user programmable, automated wind protector expedites the splicing process by automatically closing to initiate the splice process, and opening upon splice completion. These automated features reduce the steps needed to execute a splice resulting in greater splicing efficiencies. An auto-start "clamshell design" tube heater applies heat to both sides of the splice protection sleeve resulting in a 40-second shrink time for 12-fiber ribbon. The result is a total splice process time of approximately 55 seconds! Ruggedness and durability are greatly enhanced by a mirror-less optical system and "severe-impact resistant" monitor. An innovative transit case doubles as a built-in or mobile workstation. In an industry first, the 70R+ is also equipped with Bluetooth® technology. This allows the splicer to actively communicate with Bluetooth enabled fiber preparation accessories making maintenance of fiber preparation tools easier than ever!



In case with lid detached

#### Features

- Bluetooth wireless communication
- Automated and programmable wind protector
- 40-second automated tube heater
- Fully ruggedized for shock, dust and moisture
- Li-ion battery with 110 splices/shrinks per charge
- On-board training and support videos
- Multi-function transit case with integrated workstation

#### Ordering Information

DESCRIPTION	AFL NO.
<b>70R+ Fusion Splicer (machine only)</b> <b>Includes:</b> ADC-18 AC Adapter, ACC-14 AC Cord, ELCT2-20A Spare Electrodes (pair), FH-70-12 Fiber Holder, USB Cable, Alcohol Dispenser, Screw Driver, Sleeve Loader, Splicer Carrying Strap, Quick Reference Guide, Video Instruction Manual and CC30 Transit Case with Carrying Strap	S015669
<b>70R+ Fusion Splicer Kit (with cleaver)</b> <b>Includes:</b> CT50 Cleaver, RS03 Stripper, ADC-18 AC Adapter, ACC-14 AC Cord, ELCT2-20A Spare Electrodes (pair), FH-70-12 Fiber Holder, USB Cable, Alcohol Dispenser, Screw Driver, Sleeve Loader, Splicer Carrying Strap, Quick Reference Guide, Video Instruction Manual and CC30 Transit Case with Carrying Strap	S015670
<b>70R+ Fusion Splicer Kit (with cleaver, battery and cord)</b> <b>Includes:</b> BTR-09 Battery, DCC-18 Battery Charge Cord, CT50 Cleaver, RS03 Stripper, ADC-18 AC Adapter, ACC-14 AC Cord, ELCT2-20A Spare Electrodes (pair), FH-70-12 Fiber Holder, USB Cable, Alcohol Dispenser, Screw Driver, Sleeve Loader, Splicer Carrying Strap, Quick Reference Guide, Video Instruction Manual and CC30 Transit Case with Carrying Strap	S015671
<b>70R+ Fusion Splicer Kit without Bluetooth technology (with cleaver, battery and cord)</b> <b>Includes:</b> BTR-09 Battery, DCC-18 Battery Charge Cord, CT08 Cleaver, RS01 Stripper, ADC-18 AC Adapter, ACC-14 AC Cord, ELCT2-20A Spare Electrodes (pair), FH-70-12 Fiber Holder, USB Cable, Alcohol Dispenser, Screw Driver, Sleeve Loader, Splicer Carrying Strap, Quick Reference Guide, Video Instruction Manual and CC30 Transit Case with Carrying Strap	S017075
One Year Extended Warranty	S012996
Two Year Extended Warranty	S013000

## Fujikura 70R+ Fusion Splicer

### Accessories Recommended for the 70R+

DESCRIPTION	AFL NO.
<b>Cleavers and Strippers</b>	
CT50 Cleaver	S017030
RS01 Thermal Stripper	S016815
RS02 Thermal Stripper	S016816
RS03 Thermal Stripper	S016817
<b>Fiber Holders (pairs)</b>	
FH-50-10	S013824
FH-50-8	S013820
FH-50-6	S013816
FH-50-4	S013812
FH-50-2	S013808
FH-70-12	S017119
FH-70-250 (250 µm coated single fiber)	S017111
FH-70-900 (900 µm jacketed single fiber)	S017113
FH-60-LT900 (pair)	S015181
<b>FUSEConnect® Accessories</b>	
FH-FC-20 (900 µm within 2.0 mm sheathing) (each)	S014696
FH-FC-30 (900 µm within 3.0 mm sheathing) (pair)	S014695
FH-FC-900 (900 µm cable) (each)	S014697
CLAMP-FC-2000 (pair)	S014705
CLAMP-FC-3000 (pair)	S014704

DESCRIPTION	AFL NO.
<b>Batteries and Power Cords</b>	
ADC-18 AC Adapter	S015585
BTR-09 Battery and DCC-18 Charge Cord	S016780
BTR-09 Battery	S015581
DCC-18 Battery Charge Cord	S015582
DCC-12 Power Cord (connects ADC-18 to cigarette lighter socket)	S013552
DCC-13 Power Cord (connects ADC-13 to power source via alligator clips)	S013556
ACC-14 AC Power Cord	S014536
<b>Miscellaneous</b>	
ELCT2-20A Electrodes	S013532
Portable Tripod Workstation (see product profile for more detail)	S014773
ASW-02 Splicing Workstation (see product profile for more detail)	S010532
JP-06 J-PLATE (70/19 Series)	S016100
FST-12 Fiber Separation Tool	S014012
FAT-04 Fiber Arrangement Tool	S010212
FAA-03A Ribbon Forming Adhesive (4 oz. bottle)	S008720
FAA-03A Ribbon Forming Adhesive (0.5 liter bottle)	S008622
CC-30 Transit Case	S015587
Splicer V-Groove Cleaning Kit	S014397

### Specifications

PARAMETER	VALUE
Model	FSM-70R+ Fusion Splicer
Applicable Fibers	Single-mode (G.652 & G.657), Multimode (G.651), DS (G.653), NZDS (G.655)
Fiber Count	Single, 2, 4, 5, 6, 8, 10, 12
Cladding Diameter	125 µm
Coating Diameter	Ribbon: 0.25 mm to 0.4 mm, Single: 250 µm and 900 µm
Fiber Cleave Length	10 mm
Typical Average Splice Loss	0.05 dB with SM, 0.02 dB with MM, 0.08 dB with DS, 0.08 dB with NZDS; measured by cut-back method relevant to ITU-T standards
Splicing Time	Typical 15 seconds with standard single-mode fiber
Arc Calibration Method	Automatic, real-time by using results of previous splice when in AUTO mode; manual arc calibration function available
Splicing Modes	100 preset and user programmable modes
Splice Loss Estimate	Based upon dual camera cladding alignment data
Storage of Splice Result	Last 2000 splice results stored in the internal memory
Fiber Display	X or Y, or both X and Y simultaneously; front or rear monitor display options with automatic image orientation
Magnification	35X to 90X
Viewing Method	Dual cameras with 4.7 inch TFT color LCD monitor with anti-reflective coating
Operating Condition	0 to 3,660 m above sea level, 0 to 95% RH, and -10 to 50°C respectively
Mechanical Proof Test	1.96 to 2.25 N
Tube Heater	Built-in tube heater with 30 heating modes; auto-start function
Tube Heating Time	Typical 40 seconds with FP-5 sleeve, 17 seconds with FP3 (40), 5-15 seconds with Fujikura micro sleeves
Protection Sleeve Length	60 mm, 40 mm, Micro
Splice/Heat Cycles with Battery	Typical 110 cycles with power save functions activated
Electrode Life	1,500 Arc Discharges
Power Supply	Auto voltage selection from 100 to 240V AC or 10 to 15V DC with ADC-18, 14.8V DC with BTR-09 battery
Terminals	USB 2.0 (USB-B type) for PC communication and Mini-DIN (6-pin) for RS02/RS03
Wind Protection	Maximum wind velocity of 15m/s (34 mph)
Dimensions	146 W x 159 D x 150 H (mm) / 5.7 W x 6.3 D x 5.9 H (inches)
Weight	2.3 kg (5.1 lbs) with AC adapter; 2.5 kg (5.5 lbs) with battery