GN NetTest CMA4000i CMA4442 Specs Provided by www.AAATesters.com

CMA4000 Specifications	Provided by www.AAATesters.com			
Display	VGA LCD Display (8.4" color or 8.2" monochrome)			
Mass Storage	Up to 125 traces internal storage. Over 65,000 traces with optional hard drive. Up to 180 traces for a standard 3.5 inch, 1.44 MB floppy disk. Floppy disk drive comes standard			
Stored Data Points	up to 16,000			
Group Refractive Index Setting	1.400000 - 1.699999			
Loss Modes	ORL, 2-point, 2-point LSA, dB/KM, dB/KM LSA, splice, reflectance			
Trace Compare Modes	Overlay, Delta Trace Compare, Align			
Data Acquisition	Real Time, Fast Scan, Medium Scan, Slow Scan, Timed Average (user selectable)			
Information Output	Trace display, FAS event table, integrated trace display with event information window, header page, measurement parameters, ASCII report			
Analysis	High speed integrated fiber analysis			
Vertical Scale Settings	0.125/0.25/0.5/1/2/4/8 dB (module dependent)			
Horizontal Scale Settings	0.001 km/div. to 0.448 km/div @ 2 km; 0.001 km/div. to 57.304 km/div. @ 256 km (IOR = 1.5)			
I/O Ports	Standard: Integral alpha-numeric keyboard, (2) RS-232 Serial, (1) Parallel, VGA, Mouse, External Keyboard Port			
Language Capability	English standard (others per reques	st and may require hard drive option)		
Physical Dimensions & Weight	9.5" H x 13.5" W x 3.75" D (24.1 x 34.3 x 9.5 cm) / 11.0 lbs. (4.9 kg) Includes mainframe, battery and one module			
Power	includes mainmaine, battery and of	ile module		
Power Supply	Autoswitching 92-132 VAC, 47-6 184-264 VAC, 47-63 Hz	i3 Hz [weight 1.7 lbs. (.77 kg)]		
Battery	Sealed Lead Acid Battery Pack [wei	ght 1.4 lbs (0.63 kg)]		
Battery Life	up to 9 hours maximum per battery, depending on operating mode			
Recharge Time	1.5 - 2 hours			
Environmental				
Operation: Temperature Humidity Maximum Altitude	AC Power 0°C to 45°C (32°F to 122°F) 95% RH max., non-condensing 50,000 feet	Battery 0°C to 40°C (32°F to 104°F) 95% RH max., non-condensing 50,000 feet		
Storage: Temperature Humidity Maximum Altitude	-25°C to 60°C (-13°F to 140°F) 95% RH max., non-condensing 50,000 feet			

Optical Module Specifications [All measurements made using FC/SPC connectors at 25°C (77°F)]

Models	4415	4414	4413
Center Wavelength	1310 nm ± 20 nm	1550 nm ± 30 nm	1310 nm ± 20 nm
	1550 nm ± 30 nm		
Fiber Type	Singlemode 9/125µ	Singlemode 9/125µ	Singlemode 9/125µ
Spectral Width (RMS)	1310 nm: ≤ 10 nm	1550 nm: ≤ 10 nm	1310 nm: ≤ 10 nm
	1550 nm: ≤ 10 nm		
Dynamic Range ¹	1310 nm: 30 dB	1550 nm: 28 dB	1310 nm: 30 dB
(SNR = 1)	1550 nm: 28 dB		
Initial Reflective Deadzone ²	1310 nm: 3 meters (typical)	1550 nm: 3 meters (typical)	1310 nm: 3 meters (typical)
	1550 nm: 3 meters (typical)		
Initial Non-Reflective Deadzone ²	1310 nm: 10 meters (typical)	1550 nm: 12 meters (typical)	1310 nm: 10 meters (typical)
	1550 nm: 12 meters (typical)		
Pulsewidth	10 ns to 10µs		
Distance Resolution	0.0001 km; 0.1 meters; 0.001 kft, 1	ft, 0.0001 mi	
Distance Sampling	0.25, 0.5, 1, 2, 4, 8, 16 meters (rang	je dependent)	
Distance Accuracy	0.0025% of distance measurement \pm distance resolution \pm index uncertainty		
Distance Range Setting	2/4/8/16/32/64/128/256 km	-	
Loss Resolution	0.001 dB		
Laser Safety	Meets CDRH Class 1 Requirements	(Eve Safe) 21 CFR	

Models	4425	4424	4423	
Center Wavelength	1310 nm ± 20 nm	1550 nm ± 20 nm	1310 nm ± 20 nm	
	1550 nm ± 20 nm			
Fiber Type	Singlemode 9/125µ	Singlemode 9/125µ	Singlemode 9/125µ	
Spectral Width (RMS)	1310 nm: ≤ 10 nm	1550 nm: ≤ 10 nm	1310 nm: ≤ 10 nm	
	1550 nm: ≤ 10 nm			
Dynamic Range ¹	1310 nm: 36 dB	1550 nm: 34 dB	1310 nm: 36 dB	
(SNR = 1)	1550 nm: 34 dB			
Initial Reflective Deadzone ²	1310 nm: 3 meters (typical)	1550 nm: 3 meters (typical)	1310 nm: 3 meters (typical)	
	1550 nm: 3 meters (typical)			
Initial Non-Reflective Deadzone ²	1310 nm: 10 meters (typical)	1550 nm: 12 meters (typical)	1310 nm: 10 meters (typical)	
	1550 nm: 12 meters (typical)			
Pulsewidth	10 ns to 10µs			
Distance Resolution	0.0001 km; 0.1 meters; 0.001 kft, 1	ft, 0.0001 mi		
Distance Sampling	0.25, 0.5, 1, 2, 4, 8, 16 meters (rang	0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent)		
Distance Accuracy	0.0025% of distance measurement \pm distance resolution \pm index uncertainty			
Distance Range Setting	2/4/8/16/32/64/128/256 km			
Loss Resolution	0.001 dB			
Laser Safety	Meets CDRH Class 1 Requirements	(Eye Safe) 21 CFR		

Models	4438	4436	4534
Center Wavelength	1550 nm ± 20 nm	1310 nm ± 20 nm	1550 nm ± 20 nm
		1550 nm ± 20 nm	
Fiber Type	Singlemode	Singlemode 9/125µ	Singlemode 9/125µ
Spectral Width (RMS)	≤15 nm	1310 nm: ≤ 10 nm	1550 nm: ≤ 10 nm
		1550 nm: ≤ 10 nm	
Dynamic Range ¹	46.0 dB	1310 nm: 40 dB	1550 nm: 40 dB
(SNR = 1)		1550 nm: 40 dB	
Initial Reflective Deadzone ²	3 meters	1310 nm: 3.5 meters (typical)	1550 nm: 3.5 meters (typical)
		1550 nm: 3.5 meters (typical)	
Initial Non-Reflective Deadzone ²	5 meters	1310 nm: 6 meters (typical)	1550 nm: 6 meters (typical)
		1550 nm: 6 meters (typical)	
Pulsewidth		10 ns to 20µs (wavelength dependent	t)
Distance Resolution	0.0001 km; 0.1 meters; 0.001 kft, 1 ft, (0.001 mi	
Distance Sampling	0.25, 0.5, 1, 2, 4, 8, 16 meters (range d	ependent)	
Distance Accuracy	0.0025% of distance measurement \pm distance	stance resolution ± index uncertainty	
Distance Range Setting	2/4/8/16/32/64/128/256 km		
Loss Resolution	0.001 dB		
Laser Safety	Meets CDRH Class 1 Requirements (Eye	e Safe) 21 CFR	

Notes:

1. Subtract approximately 2 dB of range to 98% peak noise. Bellcore TR-TSY-000196 Issue 2

2. Using Bellcore TR-TSY-000196 Issue 2. Deadzones measured on -45 dB reflections.

Models	4442	4441	4440		
Center Wavelength	850 nm ± 20 nm	1300 nm ± 20 nm	850 nm ± 20 nm		
	1300 nm ± 20 nm				
Fiber Type	Multimode	Multimode	Multimode		
Spectral Width (RMS)	850 nm: ≤ 10 nm	1300 nm: ≤ 10 nm	850 nm: ≤ 10 nm		
	1300 nm: ≤ 10 nm				
Dynamic Range ¹	850 nm: 23 dB	1300 nm: 26 dB	850 nm: 23 dB		
(SNR = 1)	1300 nm: 26 dB				
Initial Reflective Deadzone ²	850 nm: 3.5 meters (typical)	1300 nm: 3 meters (typical)	850 nm: 3.5 meters (typical)		
	1300 nm: 3 meters (typical)				
Initial Non-Reflective Deadzone ²	850 nm: 6.5 meters (typical)	1300 nm: 7 meters (typical)	850 nm: 6.5 meters (typical)		
	1300 nm: 7 meters (typical)				
Pulsewidth	4 ns to 1µs (wavelength dependent)			
Distance Resolution	0.0001 km; 0.1 meters; 0.001 kft, 1 t	ft, 0.0001 mi			
Distance Sampling	0.25, 0.5, 1, 2, 4, 8 meters (range dependent)				
Distance Accuracy	0.0025% of distance measurement \pm distance resolution \pm index uncertainty				
Distance Range Setting	2/4/8/16/32/64 km				
Loss Resolution	0.001 dB	0.001 dB			
Laser Safety	Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR			

13 13 13 15 Fiber Type Spectral Width (RMS) 85 13 13 13 13 13 13 13 13 13 13 13 13 13 13 13 15 Dynamic Range ¹ 13 13 13 13	50 nm \pm 20 nm 300 nm \pm 20 nm 310 nm \pm 20 nm 550 nm \pm 20 nm fultimode and Singlemode 50 nm: \leq 10 nm 300 nm: \leq 10 nm 550 nm: \leq 10 nm 550 nm: \leq 10 nm 50 nm: 23 dB 300 nm: 26 dB	850 nm \pm 20 nm 1300 nm \pm 20 nm 1310 nm \pm 20 nm 1550 nm \pm 30 nm Multimode and Singlemode 850 nm: \leq 10 nm 1300 nm: \leq 10 nm 1310 nm: \leq 10 nm 1550 nm: \leq 10 nm 850 nm: 21 dB
13 15 Fiber Type Mi Spectral Width (RMS) 85 13 13 13 13 Dynamic Range ¹ 85 (SNR = 1) 13	310 nm \pm 20 nm 550 nm \pm 20 nm Jultimode and Singlemode 50 nm: \leq 10 nm 300 nm: \leq 10 nm 310 nm: \leq 10 nm 550 nm: \leq 10 nm 50 nm: 23 dB 300 nm: 26 dB	1310 nm \pm 20 nm 1550 nm \pm 30 nm Multimode and Singlemode 850 nm: \leq 10 nm 1300 nm: \leq 10 nm 1310 nm: \leq 10 nm 1310 nm: \leq 10 nm 1550 nm: \leq 10 nm
15Fiber TypeMiSpectral Width (RMS)8513131315Dynamic Range85(SNR = 1)1313	550 nm ± 20 nm 1ultimode and Singlemode 50 nm: ≤ 10 nm 300 nm: ≤ 10 nm 310 nm: ≤ 10 nm 550 nm: ≤ 10 nm 50 nm: 23 dB 300 nm: 26 dB	1550 nm \pm 30 nm Multimode and Singlemode 850 nm: \leq 10 nm 1300 nm: \leq 10 nm 1310 nm: \leq 10 nm 1550 nm: \leq 10 nm
Fiber Type Mr Spectral Width (RMS) 85 13 13 13 15 Dynamic Range ¹ 85 (SNR = 1) 13 13	Jultimode and Singlemode 50 nm: \leq 10 nm 300 nm: \leq 10 nm 310 nm: \leq 10 nm 550 nm: \leq 10 nm 50 nm: 23 dB 300 nm: 26 dB	Multimode and Singlemode $850 \text{ nm}: \le 10 \text{ nm}$ $1300 \text{ nm}: \le 10 \text{ nm}$ $1310 \text{ nm}: \le 10 \text{ nm}$ $1550 \text{ nm}: \le 10 \text{ nm}$ 850 nm: 21 dB
Spectral Width (RMS) 85 13 13 15 15 Dynamic Range ¹ 85 (SNR = 1) 13 13 13	50 nm: \leq 10 nm 300 nm: \leq 10 nm 310 nm: \leq 10 nm 550 nm: \leq 10 nm 50 nm: 23 dB 300 nm: 26 dB	850 nm: ≤ 10 nm 1300 nm: ≤ 10 nm 1310 nm: ≤ 10 nm 1550 nm: ≤ 10 nm 850 nm: 21 dB
13 13 15 Dynamic Range ¹ 85 (SNR = 1) 13 13	300 nm: ≤ 10 nm 310 nm: ≤ 10 nm 550 nm: ≤ 10 nm 50 nm: 23 dB 300 nm: 26 dB	1300 nm: ≤ 10 nm 1310 nm: ≤ 10 nm 1550 nm: ≤ 10 nm 850 nm: 21 dB
13 15 Dynamic Range ¹ 85 (SNR = 1) 13 13	310 nm: ≤ 10 nm 550 nm: ≤ 10 nm 50 nm: 23 dB 300 nm: 26 dB	1310 nm: ≤ 10 nm 1550 nm: ≤ 10 nm 850 nm: 21 dB
15 Dynamic Range ¹ 85 (SNR = 1) 13 13	550 nm: ≤ 10 nm 50 nm: 23 dB 300 nm: 26 dB	1550 nm: ≤ 10 nm 850 nm: 21 dB
Dynamic Range ¹ 85 (SNR = 1) 13 13 13	50 nm: 23 dB 300 nm: 26 dB	850 nm: 21 dB
(SNR = 1) 13 13	300 nm: 26 dB	
13		
		1300 nm: 24 dB
4 🗖	310 nm: 21.5 dB	1310 nm: 32 dB
15	550 nm: 21 dB	1550 nm: 30 dB
nitial Reflective Deadzone ² 85	50 nm: 3.5 meters (typical)	850 nm: 3.5 meters (typical)
13	300 nm: 2.5 meters (typical)	1300 nm: 2.5 meters (typical)
13	310 nm: 3 meters (typical)	1310 nm: 3 meters (typical)
15	550 nm: 3 meters (typical)	1550 nm: 3 meters (typical)
nitial Non-Reflective Deadzone ² 85	50 nm: 6.5 meters (typical)	850 nm: 6.5 meters (typical)
13	300 nm: 7 meters (typical)	1300 nm: 7 meters (typical)
13	310 nm: 10 meters (typical)	1310 nm: 15 meters (typical)
15	550 nm: 12 meters (typical)	1550 nm: 20 meters (typical)
Pulsewidth 4 r	ns to 10 µs (wavelength dependent)	4 ns to 10 μ s (wavelength dependent)
Distance Resolution 0.0	.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi	0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi
Distance Sampling 0.2	.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent)	0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent)
	.0025% of distance measurement \pm distance esolution \pm index uncertainty	0.0025% of distance measurement \pm distance resolution \pm index uncertainty
Distance Range Setting 2/4	/4/8/16/32/64/128/256 km (wavelength dependent)	2/4/8/16/32/64/128/256 km (wavelength dependent)
Loss Resolution 0.0	.001 dB	0.001 dB
Laser Safety Me	leets CDRH Class 1 Requirements (Eye Safe) 21 CFR	Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR

Notes:

1. Subtract approximately 2 dB of range to 98% peak noise. Bellcore TR-TSY-000196 Issue 2 2. Using Bellcore TR-TSY-000196 Issue 2. Deadzones measured on -45 dB reflections.

Models	4461	4462
Center Wavelength	1240 nm ± 6 nm	1240 nm ± 6 nm
		1310 nm ± 20 nm
Fiber Type	Singlemode	Singlemode
Spectral Width (RMS)	1240 nm: ≤ 15 nm	1240 nm: ≤ 15 nm
_		1310 nm: ≤ 15 nm
Dynamic Range ¹	1240 nm: 36 dB	1240 nm: 34 dB
(SNR = 1)		1310 nm: 34 dB
Initial Reflective Deadzone ²	1240 nm: 3 meters (typical)	1240 nm: 3 meters (typical)
		1310 nm: 3 meters (typical)
Initial Non-Reflective Deadzone ²	1240 nm: 10 meters (typical)	1240 nm: 10 meters (typical)
		1310 nm: 10 meters (typical)
Pulsewidth		
Distance Resolution	0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi	0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi
Distance Sampling	0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent)	0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent)
Distance Accuracy	0.0025% of distance measurement ± distance	0.0025% of distance measurement ± distance
-	resolution \pm index uncertainty	resolution \pm index uncertainty
Distance Range Setting	2/4/8/16/32/64/128/256 km	2/4/8/16/32/64/128/256 km
Loss Resolution	0.001 dB	0.001 dB
Laser Safety	Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR	Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR
Models	4463	4464
Center Wavelength	1240 nm ± 6 nm	1240 nm ± 6 nm
-	1550 nm ± 20 nm	1625 nm ± 10 nm
Fiber Type	Singlemode	Singlemode
Spectral Width (RMS)	1240 nm: ≤ 15 nm	1240 nm: ≤ 15 nm
	1550 nm: ≤ 15 nm	1625 nm: ≤ 15 nm
Dynamic Range ¹	1240 nm: 36 dB	1240 nm: 36 dB
(SNR = 1)	1550 nm: 34 dB	1625 nm: 36 dB
Initial Reflective Deadzone ²	1240 nm: 3 meters (typical)	1240 nm: 3 meters (typical)
	1550 nm: 3 meters (typical)	1625 nm: 3.5 meters (typical)
Initial Non-Reflective Deadzone ²	1240 nm: 10 meters (typical)	1240 nm: 10 meters (typical)
	1550 nm: 12 meters (typical)	1625 nm: 15 meters (typical)
Pulsewidth		
Distance Resolution	0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi	0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi
Distance Sampling	0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent)	0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent)
Distance Accuracy	0.0025% of distance measurement ± distance	0.0025% of distance measurement ± distance
2.5.4.1.007.0004.009	resolution \pm index uncertainty	resolution \pm index uncertainty
Distance Range Setting	2/4/8/16/32/64/128/256 km	2/4/8/16/32/64/128/256 km
Loss Resolution	0.001 dB	0.001 dB
Laser Safety	Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR	Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR
Luser survey		
Models	4471	4472
Center Wavelength	1625 nm ± 10 nm	1310 nm ± 20 nm
		$1625 \text{ nm} \pm 10 \text{ nm}$
Fiber Type	Singlemode	Singlemode
Spectral Width (RMS)	1625 nm: ≤ 10 nm	1310 nm: \leq 10 nm
	1023 1111. 2 10 1111	1625 nm: ≤ 10 nm
Dynamic Range ¹	1625 nm: 26 dP	
	1625 nm: 36 dB	1310 nm: 36 dB
(SNR = 1) Initial Reflective Deadzone ²	1625 pm; 4 motors (turical)	1625 nm: 36 dB
	1625 nm: 4 meters (typical)	1310 nm: 3 meters (typical)

1625 nm: 12 meters (typical) Pulsewidth Distance Resolution 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi Distance Sampling 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance 0.0025% of distance measurement ± distance Distance Accuracy resolution ± index uncertainty resolution ± index uncertainty 2/4/8/16/32/64/128/256 km 2/4/8/16/32/64/128/256 km Distance Range Setting Loss Resolution 0.001 dB 0.001 dB Laser Safety Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR

1625 nm: 12 meters (typical)

Initial Non-Reflective Deadzone²

1625 nm: 4 meters (typical)

1310 nm: 10 meters (typical)

Models	4473
Center Wavelength	1550 nm ± 20 nm
	1625 nm ± 10 nm
Fiber Type	Singlemode
Spectral Width (RMS)	1550 nm: ≤ 10 nm
	1625 nm: ≤ 10 nm
Dynamic Range ¹	1550 nm: 34 dB
(SNR = 1)	1625 nm: 36 dB
Initial Reflective Deadzone ²	1550 nm: 4 meters (typical)
	1625 nm: 4 meters (typical)
Initial Non-Reflective Deadzone ²	1550 nm: 12 meters (typical)
	1625 nm: 12 meters (typical)
Pulsewidth	
Distance Resolution	0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi
Distance Sampling	0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent)
Distance Accuracy	0.0025% of distance measurement \pm distance resolution \pm index uncertainty
Distance Range Setting	2/4/8/16/32/64/128/256 km
Loss Resolution	0.001 dB
Laser Safety	Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR

Notes:

1. Subtract approximately 2 dB of range to 98% peak noise. Bellcore TR-TSY-000196 Issue 2 2. Using Bellcore TR-TSY-000196 Issue 2. Deadzones measured on -45 dB reflections.

Multi-Test Functions

Dual Source (441X and 442X optics only; factory installed)

Output-10 dBm (typical)Transmission ModeCW, 1 KHz and 2 KHzOutput Fiber9/125µm SM fiberOptical ConnectorSame as OTDRModes of OperationCW, 1 KHz and 2 KHzStability± 0.2 dB (8 hours)Spectral WidthSame as OTDRSafetySame as OTDR	
Optical Meter (factory installed) +20 dBm meter option available	
Detector Type2 mm Ge PIN photodiodeWavelength $800 - 1800 \text{ nm}$ Range $+10 \text{ to } -55 \text{ dBm or } +20 \text{ to } -45 \text{ dBm with AM460 filterCalibrated Wavelengths3 total: 850, 1310, 1550Universal ConnectorYes (use AM-430-xx adapter caps)Resolution0.01 \text{ dB, dBm, } 0.01\% WattsStore Reference ModeYesAccuracy1\pm 4\% (\pm 0.18 \text{ dB}) @ \pm 5 \text{ dBm to } -50 \text{ dBm}\pm 8\% (\pm 0.36 \text{ dB}) @ \pm 10 \text{ dBm to } \pm 5 \text{ dBm and}@ -50 dBm to -55 dBmLinearity0.04 \text{ dB, } \pm 5 \text{ dBm to } 50 \text{ dBm}$	r
Linearity ± 0.04 dB, +5 dBm to -50 dBm	

Visual Fault Locator (field installed)

Wavelength	635 ± 10 nm
Output	0 dBm
Transmission Mode	CW or 2 Hz
Output Fiber	9/125µm, SM fiber
Optical Connector	FC, SC, ST - fixed connector
Safety	IEC 825 Class 2, FDA (21 CFR 1040. 10 class 2)

Note:

1. Specification applies to +10 dBm meter not to +20 dBm meter.

CMA4000 Optional Accessories (must be added as separate line item):

TD-400	Hard transit case	TD-459US	US style keyboard
TD-410	Deluxe soft case	TD-459GE	German CE style keyboard
TD-415	Soft carry bag	TD-459FR	French CE style keyboard
TD-405	Printer w/cable	TD-459SP	Spanish CE style keyboard
TD-309	Printer paper (5 rolls/pack)	TD-459IT	Italian CE style keyboard
TD-409	Case of paper (5 packs/case)	TD-30163	Additional User's Manual
TD-453	12 v lead acid battery	TD-30162	Additional Training Manual
TD-29621	12 v DC power adapter	TD-30711	Parallel cable - DB25M to DB25M
TD-30710	Serial cable DB9F to DB9F (null)	TD-30712	Serial cable DB9F to DB9M (straight)

CMA4000 Mainframe:

Control Unit:

• 1 VGA port

• 1 carry strap

P/N TD-14XXX PC-based modular platform

Standard Accessories:

٠	8-inch	VGA	LCD	disp	lay
---	--------	-----	-----	------	-----

• User's & Training Manuals

- 2 serial ports • Multi-tasking operating system • 1 parallel port
 - 1 mouse port
 - 1 PS/2 keyboard port
 - 12 v rechargeable battery (qty 2)
 - Floppy drive
 - Built-in keyboard
- AC adapter/charger • AC line cord (choose style - see below)

• Internal memory (up to 140 traces)

AC Power Cord Options:

TD-11685	US power cord	TD-30362	Australian power cord
TD-30358	Euro power cord	TD-30359	UK power cord
TD-30361	Italian power cord	TD-30360	Swiss power cord

OTDR/Source Connector Adapter:

Adapters for PC and Ultra Polish:


UC-130-10	Biconic	UC-130-35	SMA 905/906
UC-130-15	DIN 47256	UC-130-40	Diamond HP HMS-10
UC-130-20	D4	UC-130-45	Diamond HP HMS-0
UC-130-25	FC	UC-130-50	Diamond HP-HMS-10/A
UC-130-30	ST	UC-130-55	SC

Adapters for Angle Polish:

UC-130-60	FC NTT	UC-130-70	DIN/HRL-10
UC-130-60A	FC Seiko Giken	UC-130-75	ST
UC-130-65	SC	UC-130-80	Diamond E-2000

Meter Connector Adapter (select one when ordering power meter):

AM-430-10	Biconic	AM-430-50	ST
AM-430-15	D4	AM-430-75	VFO/PFO
AM-430-20	SMA 906	AM-430-85	DIN
AM-430-25	Diamond GFS-3	AM-430-90	SC
AM-430-45	FC	AM-430-100	FDDI



No. of Concession, Name

Our equipment is constantly being improved. Hence, specifications are subject to change without notice.

www.annettest.com