



# Olympus OMNIScan SX Specs Provided by www.AAATesters.com

# OmniScan SX

Smaller, Lighter ... Still an OmniScan













- Cost-efficient, single-group
- Two-axis encoding and data archiving capacity
- Conventional UT, TOFD, and 16:64PR PA capabilities
- 8.4 in. (21.3 cm) touch screen with OmniScan interface
- Compact, lightweight design

## The Lightest and Most User-Friendly OmniScan

### **OmniScan SX**

Olympus is proud to introduce the OmniScan® SX, a flaw detector that benefits from more than 20 years of phased array experience and shares the OmniScan DNA. For improved ease of use, the OmniScan SX features a new streamlined software interface displayed on an 8.4 in. (21.3 cm) touch screen. A single-group and non-modular instrument, the OmniScan SX is easy to operate and cost-effective for less demanding applications.

The OmniScan SX comes in two models: the SX PA and SX UT. The SX PA is a 16:64PR phased array unit, which, like the UT-only SX UT, is equipped with a conventional UT channel for pulse-echo, pitch-catch or TOFD inspection. Compared to the OmniScan MX2, the SX is 33% lighter and 50% smaller, offering an unprecedented level of portability for an OmniScan.



### **Setup**

Inspection setup can be performed in NDT SetupBuilder, and imported directly, via SD card or USB key, to the OmniScan SX. Then, only a few basic operations are required in the instrument, such as setting the gate and range, before acquisition can begin. It is also very easy to create a setup right in the OmniScan SX, thanks to the following features:

- Automatic probe recognition.
- One-step, preconfigured application Wizard.
- Weld Overlay and RayTracing simulation.

#### **Calibration**

To achieve a code-compliant inspection, the Calibration Wizard ensures that every focal law in every group is the direct equivalent of a single-channel conventional flaw detector. The user is guided step-by-step through the required calibrations, including Velocity, Wedge Delay, Sensitivity, TCG, DAC, AWS, and encoder calibrations. Now, TOFD PCS calibration and lateral wave straightening can be performed automatically.

### **Acquisition**

The OmniScan SX enables easy configuration of inspection parameters for either manual, one-line, or raster encoded scans. The acquisition is displayed in real time through user-selectable views and offers the ability to store data on a hot-swappable SD card or USB 2.0 device.

- Intelligent layouts.
- · Full-screen mode for better visualization of defects.
- Synchronization and measurements can be processed using different gate combinations.

### **Data Analysis and Reporting**


- Data, reference, and measurement cursors for defect sizing.
- Extensive readings database and predefined lists for trigonometry, flaw statistics on axes, volumetric position information, code-based acceptance criteria, corrosion mapping statistics, and more
- Views are linked for interactive analysis and automatically updated when performing off-line gate repositioning.
- Optimized preconfigured layouts for quick and simple length, depth, and height sizing of flaws.

Whether you prefer performing data analysis on a computer or simply wish to maximize the time your OmniScan is at work in the field, OmniPC or TomoView are the perfect software companions for your OmniScan.

## Affordable and Portable Go a Long Way....

The Omniscan® SX provides Olympus with a new and versatile tool to add to its arsenal of innovative and creative complete market solutions aimed at simplifying your workflow and improving overall productivity.

### **Phased Array Weld Inspection**



The OmniScan PA is at the heart of the manual and semiautomated phased array weld inspection solutions developed by Olympus for the oil and gas industry. These systems can be used for inspection in compliance with ASME, API, and other code criteria, while offering high-speed detection capabilities, and facilitating indication interpretation.

### **Corrosion Mapping and Composite Inspection**



Zero-degree inspection just became even more accessible with the arrival of the OmniScan SX. For corrosion or composite inspection, Olympus offers field-proven solutions for detection of anomalies or wall loss.

### **TOFD Weld Inspection**



TOFD is an easy and efficient approach for primary detection of weld defects. It is quick, cost-effective and capable of sizing defects present in the volume of the weld, a problematic area for manufacturing defects.

### **Component Inspection**



Using ultrasonic techniques, inspection of components can detect cracks, wall loss, and other damage. With the capacity for both angle and linear zero-degree beams, the OmniScan SX is a very cost-efficient solution for this type of single-group inspection.

### OmniScan® SX Specifications\*

Housing		
Overall dimensions	267 mm × 208 mm × 94 mm	
(W x H x D)	(10.5 in. × 8.2 in. × 3.7 in.)	
Weight	3.4 kg (7.5 lb) with battery	
Data Storage		
Storage devices	SDHC card or most standard USB storage devices	
Data file size	300 MB	
I/O Ports		
USB ports	2 USB ports, compliant with USB 2.0 specifications	
Audio alarm	Yes	
Video output	Video out (SVGA)	
I/O Lines		
Encoder	2-axis encoder line (quadrature, up, down, or clock/direction)	
Digital input	4 digital TTL inputs, 5 V	
Digital output	3 digital outputs TTL, 5 V, 15 mA maximum per output	
Acquisition on/off switch	Yes, through configuration of a digital input	
Power output line	5 V, 500 mA power output line (short-circuit protected)	
Pace input	5 V TTL pace input	
Display		
Display size	21.3 cm (8.4 in.) (diagonal)	
Resolution	800 pixels x 600 pixels	
Brightness	600 cd/m <sup>2</sup>	
Viewing angles	Horizontal: -80° to 80° Vertical: -60° to 80°	
Number of colors	16 million	
Туре	TFT LCD	
Power Supply		
Battery type	Smart Li-ion battery	
Number of batteries	1	
Battery life	Minimum 6 hours under normal operating conditions	
Environmental Specification	ns	
Operating temperature range	-10 °C to 45 °C (14 °F to 113 °F)	
Storage temperature range	-20 °C to 60 °C (-4 °F to 140 °F) with battery -20 °C to 70 °C (-4 °F to 158 °F) without battery	
Relative humidity	Max. 70% RH at 45°C noncondensing	
Ingress protection rating	Designed to meet requirements of IP66	
Shockproof rating	Drop-tested according to MIL-STD-810G 516.6	



OmniScan MX2

OmniScan SX

If multigroup inspections (ex: two PA probes or combined PA + UT) are required or anticipated, Olympus recommends the OmniScan MX2. This advanced flaw detector's modular platform facilitates the upgrade path you can start with the module in your price/performance range and upgrade later to one of the many other modules available.

<u> </u>	cifications (applies to		
Connectors	1 Phased Array connector: Olympus PA connector 2 UT connectors: LEMO 00		
Number of focal laws	256		
Probe recognition	Automatic probe recognition	on	
Pulser/Receiver			
Aperture	16 elements		
Number of elements	64 elements		
Pulser	PA Channels	UT Channel	
Voltage	40 V, 80 V, and 115 V	95 V, 175 V, and 340 V	
Pulse width	Adjustable from 30 ns to 500 ns; resolution of 2.5 ns	Adjustable from 30 ns to 1,000 ns; resolution of 2.5 ns	
Pulse shape	Negative square wave	Negative square wave	
Output impedance	$35~\Omega$ (pulse-echo mode); $30~\Omega$ (pitch- catch mode)	<30 Ω	
Receiver	PA Channels	UT Channel	
Gain	0 dB to 80 dB, maximum input signal 550 mVp-p (full-screen height)	0 dB to 120 dB maximum input signal 34.5 Vp-p (full-screen height)	
Input impedance	60 $\Omega$ (pulse-echo mode); 150 $\Omega$ (pitch- catch mode)	60 $\Omega$ (pulse-echo mode); 50 $\Omega$ (pulse-receive mode)	
System bandwidth	0.6 MHz to 18 MHz (-3 dB)	0.25 MHz to 28 MHz (-3 dB)	
Beamforming			
Scan type	Sectorial or linear		
Group quantity	1		
Data Acquisition	PA Channels	UT Channel	
Digitizing frequency	400 MHz (12 bits) after interpolation per 5/4	400 MHz (12 bits) after interpolation per 4	
Maximum pulsing rate	Up to 6 kHz (C-scan)		
Data Processing	PA Channels	UT Channel	
Number of data points	Up to 8,192		
Real-time averaging	PA: 2, 4, 8, 16	UT: 2, 4, 8, 16, 32, 64	
Rectifier	RF, full wave, half wave +, half wave -		
Filtering	3 low-pass, 3 band-pass, and 5 high-pass filters	3 low-pass, 6 band-pass and 3 high-pass filters (8 low-pass filters when configured in TOFD)	
Video filtering	Smoothing (adjusted to pr	obe frequency range)	
Data Visualization			
A-scan refresh rate	A-scan: 60 Hz; S-scan: 60	) Hz	
Data Synchronization			
On internal clock	1 Hz to 6 kHz		
On encoder	On 2 axes: from 1 to 65,5	On 2 axes: from 1 to 65,536 steps	
Programmable Time-C	orrected Gain (TCG)		
Number of points	16: One TCG (time-correc	16: One TCG (time-corrected gain) curve per focal law	
Maximum slope	40 dB/10 ns		
Alarms			
Number of alarms	3		

OLYMPUS NDT INC. is ISO 9001 and 14001 certified

"All specifications are subject to change without notice.

All brands are trademarks or registered trademarks of their respective owners and third party entities.

Copyright © 2013 by Olympus.

www.olympus-ims.com



OLYMPUS NDT INC.

48 Woerd Avenue, Waitham, MA 02453, USA, Tel.: (1) 781-419-3900
12569 Gulf Freeway, Houston, TX 77034, USA, Tel.: (1) 281-922-9300

OLYMPUS NDT CANADA INC.
505, boul. du Parc-Technologique, Québec (Québec) G1P 4S9, Tel.: (1) 418-872-1155
1109 78 Ave, Edmonton (Alberta) T6P 1L8

